

PAX[®]

Momento II[™]

– unique timer with app
control feature



PAX[®]

New unique timer with exclusive features **Momento II™**


With Pax Momento II™, your towel warmer is only running when you need it to be, so you can easily lower your electricity bill without compromising on everyday luxury. Momento II™ comes with dozens of smart features that allow you to save energy, improve your indoor climate and simplify your everyday life.

How Momento II™ works

Momento II™ gives you full control over when you want your towel warmer to be on. You can configure multiple different timers directly on the warmer using the built-in button, or using the Pax Wireless app. With the app, you can also set multiple different power levels. This allows you to optimise the use of your towel warmer as it is only running when you need it to be. If you have a Pax Norte bathroom fan in the same bathroom as your towel warmer, you can pair them so the towel warmer switches on automatically when the fan's humidity sensor detects an increased humidity level, for example when you start showering.



The light is turned off when the towel warmer is off.



A red light means that the towel warmer is warm.



A blue light is illuminated when pairing with a mobile phone via Bluetooth.

WallFix™ – the smart coupling housing

All Pax towel warmers with Momento II™ are equipped with WallFix™, a smart separate coupling housing with plenty of space to make wiring and installing your towel warmer quick, smooth and straightforward.

1. Screw the coupling housing onto the wall.
2. Connect the wiring.
3. Dock the towel warmer and mount the other wall brackets.

Done!



GET IT ON
Google play

Download on the
App Store

Bluetooth

The Pax Wireless app can be downloaded from the App Store or Google Play. See Pax website for more information about Momento II™.

PAX®

New!

Pax Limbo

- lightweight and compact



By pair your towel warmer with your Norte bathroom fan you can switch the towel warmer on automatically when the humidity level in the room increases.

Pax Limbo is equipped with Momento II™ as standard.

Limbo	Art. nr
Chrome	3550-1
White/Chrome	3550-2

pax.se

Mailingaddress:
PO Box 72
SE-648 06
Hälleforsnäs

Visitingaddress:
Kattkärrsvägen 4
SE-648 31
Hälleforsnäs

Tel. +46 157-756 00
info@pax.se
009-089653
© Copyright Pax AB

20190103